

RS Part Number: **466-217**
 Specifications and dimensions



- Boxed isolator 4 pole
- ABS plastic enclosure with padlockable handle

Specifications	
Height	175 mm
Width	125 mm
Depth	90 mm
Depth including switch	134 mm
Degree of protection	IP65
Rated operational current Ie AC21A	80 A
Rated operational current Ie AC22A	63 A
Rated operational voltage Ue IEC & EN	690 V
Rated operational power AC23A 380-440V	37 kW
Rated operational power AC3 440V	22 kW
Maximum gL fuse size IEC	63 A
Rated fused short circuit capacity IEC	30 kA
Knockout size	25 mm
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	25 mm ²
Recommended tightening torque	2.0 Nm
Number of possible auxilliary contacts	1
Related products	
Neutral contact (early make/late break)	136-5280