



## Moldex 7000 Series Reusable Half Mask

**MOLDEX**

- Lightweight
- Mask body is gentle on the skin and is available in 3 sizes
- Easy to clean and maintain
- Low profile design for excellent field of vision
- Use with Moldex EASYLOCK® filter system that requires no additional clips or holders

Code	Alt Ref	Size	Price
SAF6226	700101	Small	£18.04
SAF6228	700201	Medium	£19.80
SAF6230	700301	Large	£18.48



## Moldex 9000 Series Full Face Masks

**MOLDEX**

- Excellent periphery vision
- Lightweight, with panoramic lens
- Easy to clean and maintain
- Class 2
- All filter combinations possible
- Use with Moldex EASYLOCK® filter system that requires no additional clips or holders

Code	Alt Ref	Size	Price
SAF6220	900101	Small	£112.00
SAF6222	900201	Medium	£112.00
SAF6224	900301	Large	£112.00



## Moldex EasyLock® Gas and Particulate Filters

**MOLDEX**

Moldex EasyLock® gas and particulate filters can be used on the 7000 and 9000 Series half face and full face masks. Easily connected to the mask body, a wide variety of filter combinations possible, they simply click together without the need for additional clips or filter holders. Detailed below are the various options available in terms of hazard coverage.

Code	Alt Ref	Description	Application	Pack	Price
SAF6232	901001	EasyLock® particulate filters - 9010 P1 R	Non toxic dusts, mists and fumes	20	£27.50
SAF6234	902001	EasyLock® particulate filters - 9020 P2 R	Harmful and toxic dusts, fumes and aerosols	20	£50.00
SAF6236	903001	EasyLock® particulate filters - 9030 P3 R	Harmful and toxic dusts, mists and fumes including radioactive particles and airborne biological substances or enzymes	12	£111.00
SAF6238	910001	EasyLock® gas filters - 9100 A1	Organic gases and vapours (boiling point >65°C), 1000ppm	10	£49.70
SAF6240	920001	EasyLock® gas filters - 9200 A2	Organic gases and vapours (boiling point >65°C), 5000ppm	8	£45.10
SAF6242	930001	EasyLock® gas filters - 9300 ABE1	Organic (boiling point >65°C) and inorganic gases and vapours plus acid gases, 1000ppm	10	£60.00
SAF6244	940001	EasyLock® gas filters - 9400 ABEK1	Organic (boiling point >65°C) and inorganic gases and vapours, acid gases and Ammonia, 1000ppm	10	£67.00