



3315Z0

Medium Light



The 3315Z0 LED light: the lightweight compact design houses 3AA batteries that power a single LED for 138 lumens of super bright LED light. Safety approved for the most volatile work environments ATEX Cat. 1 (Zone 0), the 3315Z0 LED light is one of the most efficient torches on the market today. The 3315Z0 LED light: Compact light, huge LED performance.

The 3315Z0 LED light: the lightweight compact design houses 3AA batteries that power a single LED for 138 lumens of super bright LED light. Safety approved for the most volatile work environments ATEX Cat. 1 (Zone 0), the 3315Z0 LED light is one of the most efficient torches on the market today. The 3315Z0 LED light: Compact light, huge LED performance.

CONFIGURATIONS

3315Z0 - Standard

DIMENSIONS

Length: 6.14"

MATERIALS

Body: Anti-static Impact Modified PC/PBT

O-Ring: EPDM

Lens: Anti-static coated Polycarbonate (PC)






COLOURS



Yellow

LIGHT SPECS

Lamp Type: LED

FL1 STANDARD	HIGH
	138 LUMENS
	19h 0mins
	146m
	5350cd
	IPX7

POWER

Battery Size: AA
Battery Type: Alkaline
Battery Quantity: 3
Batteries Included: yes
Volts: 4.5v

WEIGHT

Weight With Batteries: 6.2 oz
Weight Without Batteries: 3.7 oz

SWITCH

Switch Type: Push Button
Light Modes: On / Off

CERTIFICATIONS

ATEX Zone 0

OTHER

Minimum Pack: 1

Peli Products, S.L.U.

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com