






PCB LAYOUT (CONNECTOR TOP VIEW)

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- SHIELD BOX LEGS
- CONNECTOR LOCATION PINS

PANEL CUT OUT

3.8-5.0mm RECOMMEND
PANEL THICKNESS

RECOMMEND MINIMUM MOUNTING PITCH

RJXS8FP25HP

SERIES PREFIX
CONTACT LAYOUT (RJ45 STYLE)
GENDER
THERMOPLASTIC 3.8mm to 5.0mm WITH CAP
TRANSMISSION CLASS (CAT5e)
HORIZONTAL MOUNT (PCB THRU HOLE)
POTTED



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER		Amphenol		Amphenol Australia Pty.Ltd. 22 Industry Blvd Carrum Downs, VIC 3202	
LINEAR	ANGULAR	MATERIAL:	DRN: J.W	DATE: 24/08/2023	XLNRZ PANEL MOUNT, Horet, IP65, POTTED, WITH CAP, PANEL THICKNESS 3.8-5.0	PART NO:	REV
X .X ± .5	X° ± .1		CKD: P.M.	DATE: 24/08/2023		RJXS8FP25HP	
X.X ± .5	X°X' ± 30"		APP: P.M.	DATE: 24/08/2023		DRAWING No.	SHEET
X.X ± .5	X°X'X'' ± 15"		SCALE: NTS	SIZE: A3		55011542-100-1	2 / 2
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS							
DO NOT SCALE		FINISH: SEE COMPONENTS					
DIMENSIONS IN MILLIMETRES		 THIRD ANGLE PROJECTION					