

## IN 19 L 8-90

Screwdriver bit socket 1/2"

Code	ETIM
6157730	EC002157
EAN	UNSPSC
4010886615775	27-11-17-01
Country of origin	eCl@ss
Germany	21-04-04-02
Customs tariff number	
82079030	



### Article description

- Acc. to DIN 7422
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated

### Article information

Contents (Qty of pieces)	1	Drive connector square female [inch]	1/2"
Net weight [kg]	0,095 kg	Standard	DIN 7422 DIN 3120 - C 12,5 ISO 1174
Total length [mm]	90 mm	Width across flats l [mm]	8
Total width [mm]	22,5 mm	Backup	Ball Catching Cricket
Surface	chrome-plated	Tip length	52,0 mm
Material	Chrome-vanadium steel	Insert Ø Actuator	22,5 mm
Drive connector square female (metric)	12,5 mm		