

Specifications

Eaton MBP6KIG2



Eaton HotSwap MBP Gen2 maintenance bypass, 6000 VA, Input: Hardwired, Outputs: (2) C13, (3) C39, Hardwired, Rack-mounting kit included

Photo is representative



General Specifications

PRODUCT NAME	Eaton HotSwap MBP maintenance bypass
CATALOG NUMBER	MBP6KIG2
PRODUCT LENGTH/DEPTH	125 mm
PRODUCT HEIGHT	130 mm
PRODUCT WIDTH	177 mm
PRODUCT WEIGHT	2 kg
WARRANTY	2 year
COMPLIANCES	LVD Directive (CB) EMC Directive RoHS Directive REACH WEEE Directive Packaging Directive
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 IEC/EN 62040-3 CE UKCA Cm Ukr RCM
EAN	3553340684746
MODEL CODE	Eaton HotSwap MBP 6000i G2



Powering Business Worldwide

Product specifications

RACK SIZE	3U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	<ul style="list-style-type: none">• Maintenance Bypass• Connection cable to the UPS• Rack mounting kit• Quick start guide
TYPE OF ACCESSORY	Bypass
USED WITH	9PX Gen2 (5/6kVA) / 9SX Gen2 (5/6kVA)
RECEPTACLE	(2) C13, (3) C39
NUMBER OF OUTPUTS HARDWIRED	1
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)

Resources

MANUALS AND USER GUIDES	Eaton 9PX Gen2 Hotswap MBP Advanced user guide - EN
-------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

