


POWERMATE®



(4.19 mm) .165"

IPBS SERIES

ATED CONTACT POWER SOCKET

SPECIFICATIONS

For complete specifications see www.samtec.com?IPBS

Insulator Material: Black Liquid Crystal Polymer Contact Material: Phosphor Bronze

Plating: Sn over 50 μ" (1.27 μm) Ni Operating Temp Range: -55 °C to +105 °C Insertion Depth: (6.15 mm) .242" to (7.24 mm) .285" Wiping Distance:

VIPING DISTANCE: (0.38 mm) .015" min. Voltage Rating: 400 VAC/565 VDC Standard Creepage: (4.27 mm) .168" (-S) (1.68 mm) .066" (-D) Standard Clearance: (0.16 mm) .006" (-D) (2.16 mm) .085" (-S) (1.14 mm) .045" (-D) RoHS Compliant:

Lead-Free Solderable: Yes

IPBT/IPBS	
PINS POWERED	CURRENT RATING (PER CONTACT)
2	10.3 A
4	8.4 A
6	7.6 A
8	7.1 A
30	60 /

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality





ALSO AVAILABLE (MOQ Required)


· Other sizes

Mates with:









Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice