

HOLESAWS > BI METAL



suttontools

H125 - Bi-Metal Holesaw - Cobalt - Sutton Tools

Used for machine or hand drilling and are suited to cut steels, stainless steel, cast iron, non-ferrous materials, plastic and wood. Use Sutton Tools Venom Lubricating Fluid to increase the life of your tool when cutting metal.

Features:

- Made from Bi-Metal Cobalt HSS for toughness and longer life
- 32mm cutting depth
- Varied pitched cutting teeth reduces vibration for cleaner finish and greater accuracy
- Fast ejection slots
- International thread for use with Sutton Tools Quickfit Holesaw Arbor Item # H103 QFX

Specifications:

Material: Bi-Metal Cobalt HSS

Type: 32mm cut depth

HOLESAWS > BI METAL

Range:

Item #	Diameter (mm)	Diameter (inch)	Thread	Pilot	Arbor
H1250140	14	9/16	1/2	BD24, BD26	UA1
H1250160	16	5/8	1/2	BD24, BD26	UA1
H1250170	17	11/16	1/2	BD24, BD26	UA1
H1250190	19	3/4	1/2	BD24, BD26	UA1
H1250200	20	-	1/2	BD24, BD26	UA1
H1250210	21	13/16	1/2	BD26	UA1
H1250220	22	7/8	1/2	BD24, BD26	UA1
H1250240	24	15/16	1/2	BD24, BD26	UA1
H1250250	25	1	1/2	BD24, BD26	UA1
H1250270	27	1-1/16	1/2	BD24, BD26	UA1
H1250290	29	1-1/8	1/2	BD24, BD26	UA1
H1250300	30	1-3/16	1/2	BD24, BD26	UA1
H1250320	32	1-1/4	5/8	BD24, BD26	UA2, QFX
H1250330	33	1-5/16	5/8	BD24, BD26	UA2, QFX
H1250350	35	1-3/8	5/8	BD24, BD26	UA2, QFX
H1250370	37	1-7/16	5/8	BD24, BD26	UA2, QFX
H1250380	38	1-1/2	5/8	BD24, BD26	UA2, QFX
H1250400	40	1-9/16	5/8	BD24, BD26	UA2, QFX
H1250410	41	1-5/8	5/8	BD24, BD26	UA2, QFX
H1250430	41	1-11/16	5/8	BD24, BD26	UA2, QFX
H1250440	44	1-3/4	5/8	BD24, BD26	UA2, QFX
H1250460	46	1-13/16	5/8	BD24, BD26	UA2, QFX
H1250480	48	1-7/8	5/8	BD24, BD26	UA2, QFX
H1250510	51	2	5/8	BD24, BD26	UA2, QFX
H1250520	52	2-1/16	5/8	BD24, BD26	UA2, QFX
H1250540	54	2-1/8	5/8	BD24, BD26	UA2, QFX
H1250560	56	2-3/16	5/8	BD24, BD26	UA3, QFX
H1250570	57	2-1/4	5/8	BD24, BD26	UA3, QFX
H1250590	59	2-5/16	5/8	BD24, BD26	UA3, QFX
H1250600	60	2-3/8	5/8	BD24, BD26	UA3, QFX
H1250630	63	2-1/2	5/8	BD24, BD26	UA3, QFX
H1250650	65	2-9/16	5/8	BD24, BD26	UA3, QFX
H1250670	67	2-5/8	5/8	BD24, BD26	UA3, QFX
H1250700	70	2-3/4	5/8	BD24, BD26	UA3, QFX
H1250730	73	2-7/8	5/8	BD24, BD26	UA3, QFX

HOLESAWS > BI METAL

Range:

Item #	Diameter (mm)	Diameter (inch)	Thread	Pilot	Arbor
H1250760	76	3	5/8	BD24, BD26	UA3, QFX
H1250790	79	3-1/8	5/8	BD24, BD26	UA3, QFX
H1250830	83	3-1/4	5/8	BD24, BD26	UA3, QFX
H1250860	86	3-3/8	5/8	BD24, BD26	UA3, QFX
H1250890	89	3-1/2	5/8	BD24, BD26	UA3, QFX
H1250920	92	3-5/8	5/8	BD24, BD26	UA3, QFX
H1250950	95	3-3/4	5/8	BD24, BD26	UA3, QFX
H1250980	98	3-7/8	5/8	BD24, BD26	UA3, QFX
H1251020	102	4	5/8	BD24, BD26	UA3, QFX
H1251050	105	4-1/8	5/8	BD24, BD26	UA3, QFX
H1251080	108	4-1/4	5/8	BD24, BD26	UA3, QFX
H1251110	111	4-3/8	5/8	BD24, BD26	UA3, QFX
H1251140	114	4-1/2	5/8	BD24, BD26	UA3, QFX
H1251210	121	4-3/4	5/8	BD24, BD26	UA3, QFX
H1251270	127	5	5/8	BD24, BD26	UA3, QFX
H1251400	140	5-1/2	5/8	BD24, BD26	UA3, QFX
H1251520	152	6	5/8	BD24, BD26	UA3, QFX

HOLESAWS > BI METAL

Trade/DIY Applications:

Wood	Metal	Specialty	Masonry
Soft Wood	Steel	● PVC Plastic	Masonry
Hard Wood	Hard Steel	● Acrylic	Plasterboard
Wood & Nails	Stainless Steel	● mineral rock wool foams (EPS, PUR),	Compressed Fibre Cement
Chipboard	Aluminium	Polystyrene	Cement Sheet
Plywood	Copper / Brass	Leather	Ceramic Tile
MDF	Cast Iron	● Rubber	Hebel
Green Wood	Sheet Metal	Fibreglass	Brick
Sandwich Construction	Precious Metals	Carbon Fibre	Concrete
Pallet	Metal Pipe	Glass	Reinforced Concrete
Window Frame		Laminate	Stone
			Granite
			Marble

KEY

● Optimal ○ Effective