



Main

Range	Mureva
Product or component type	Interlocked socket
Device short name	Mureva socket
Plug, socket category	Low voltage
Poles description	3P + N + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
[In] rated current	63 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Protection type	Without protection
Product compatibility	Modular device
Plug, socket material	Housing: self-extinguishing polymer
Contacts material	Pins: stainless steel Screws: stainless steel
Connections - terminals	Captive screws
Maximum cable cross section	35 mm ²
Maximum cable outer diameter	25 mm
Cable entry	Cable gland
Thread type	Pg 21
Net weight	3 kg
Base dimension	140 x 430 mm
Height	430 mm
Width	140 mm
Depth	190 mm
Colour	Grey (RAL 7035)
Voltage colour	Red

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 62262
Fire resistance	750 °C conforming to IEC 60695-2-11
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	55