



ENGLISH

Datasheet

8 Inch Adjustable Spanner with 26.8mm Jaw Capacity

RS Stock number [541-6589](#)



Specification:

- Material: Chrome vanadium steel (CR-v steel 6150) for adjustable wrenches
- Finish: Phosphate black finish, polish jaw portion with laser scale with logo
- Hardness: Heat treated to HRC: 42 ~ 48

Contents:

1 pc-8" (200mm) wide jaw adjustable wrenches with laser metric scales (overall length - 203 mm, max jaw)

Remarks:

Torque, hardness and gauges meet din 3117 standard.