









# Verteilereinbaugeräte GREEN ELECTRIC®

## Devices for junction boxes GREEN ELECTRIC®

Artikelbezeichnung <i>Article description</i>	Bemessungsstrom <i>rated current</i>	Art.-Nr <i>Art.No.</i>	EAN-Code <i>EAN code</i>	BE <i>PUC</i>
 <p><b>Leitungsschutzschalter MCB, 3-polig</b> <i>Miniature Circuit Breaker MCB, 3-pole</i> 400 V AC In 0,5-4 A <span style="border: 1px solid black; padding: 2px;">10000</span> In 6-40 A <span style="border: 1px solid black; padding: 2px;">10000</span> <span style="border: 1px solid black; padding: 2px;">3</span> In 50-63 A <span style="border: 1px solid black; padding: 2px;">10000</span></p> <p><b>C</b></p>	1 A	7201.3100.0	4008224250115	4
	2 A	7202.3100.3	4008224250122	4
	4 A	7204.3100.9	4008224250139	4
	6 A	7206.3100.5	4008224163859	4
	10 A	7210.3100.8	4008224163866	4
	13 A	7213.3100.7	4008224163873	4
	16 A	7216.3100.6	4008224163880	4
	20 A	7220.3100.9	4008224163897	4
	25 A	7225.3100.4	4008224163903	4
	32 A	7232.3100.6	4008224163910	4
	35 A	7235.3100.5	4008224250160	4
	40 A	7240.3100.1	4008224163927	4
	50 A	7250.3100.2	4008224163941	4
	63 A	7263.3100.2	4008224163958	4
 <p><b>Leitungsschutzschalter MCB, 3polig + N</b> <i>Miniature Circuit Breaker MCB, three pole + N</i> 400 V AC In 0,5-4 A <span style="border: 1px solid black; padding: 2px;">10000</span> In 6-40 A <span style="border: 1px solid black; padding: 2px;">10000</span> <span style="border: 1px solid black; padding: 2px;">3</span> In 50-63 A <span style="border: 1px solid black; padding: 2px;">10000</span></p> <p><b>C</b></p>	0,5 A	7205.4100.9	4008224249980	3
	1 A	7201.4100.7	4008224249768	3
	2 A	7202.4100.0	4008224249799	3
	4 A	7204.4100.6	4008224249829	3
	6 A	7206.4100.2	4008224164153	3
	10 A	7210.4100.5	4008224164160	3
	13 A	7213.4100.4	4008224238052	3
	16 A	7216.4100.3	4008224164177	3
	20 A	7220.4100.6	4008224164184	3
	25 A	7225.4100.1	4008224164191	3
	32 A	7232.4100.3	4008224164214	3
	40 A	7240.4100.8	4008224164221	3
	50 A	7250.4100.9	4008224164238	3
	63 A	7263.4100.9	4008224164245	3
 <p><b>Leitungsschutzschalter MCB, 1-polig</b> <i>Miniature Circuit Breaker MCB, 1-pole</i> 230/400 V AC In 0,5-4 A <span style="border: 1px solid black; padding: 2px;">10000</span> In 6-40 A <span style="border: 1px solid black; padding: 2px;">10000</span> <span style="border: 1px solid black; padding: 2px;">3</span> In 40-63 A auf Anfrage <span style="border: 1px solid black; padding: 2px;">10000</span> <i>upon demand</i></p> <p><b>D</b></p>	0,5 A	7205.0200.2	4008224352611	12
	1 A	7201.0200.0	4008224352635	12
	2 A	7202.0200.3	4008224352642	12
	4 A	7204.0200.9	4008224352659	12
	6 A	7206.0200.5	4008224352666	12
	10 A	7210.0200.8	4008224352918	12
	13 A	7213.0200.7	4008224352925	12
	16 A	7216.0200.6	4008224352932	12
	20 A	7220.0200.9	4008224352949	12
	25 A	7225.0200.4	4008224352956	12
	32 A	7232.0200.6	4008224352963	12
 <p><b>Leitungsschutzschalter MCB, 2-polig</b> <i>Miniature Circuit Breaker MCB, 2-pole</i> 400 V AC In 10-32 A <span style="border: 1px solid black; padding: 2px;">10000</span> <span style="border: 1px solid black; padding: 2px;">3</span> 40-63 A auf Anfrage <span style="border: 1px solid black; padding: 2px;">10000</span></p> <p><b>D</b></p>	10 A	7210.2200.2	4008224353014	6
	13 A	7213.2200.1	4008224353021	6
	16 A	7216.2200.0	4008224353038	6
	25 A	7225.2200.8	4008224353052	6
	32 A	7232.2200.0	4008224353069	6
 <p><b>Leitungsschutzschalter MCB, 3-polig</b> <i>Miniature Circuit Breaker MCB, 3-pole</i> 400 V AC In 6-32 A <span style="border: 1px solid black; padding: 2px;">10000</span> <span style="border: 1px solid black; padding: 2px;">3</span> 40-63 A auf Anfrage <span style="border: 1px solid black; padding: 2px;">10000</span> <i>upon demand</i></p> <p><b>D</b></p>	6 A	7206.3200.6	4008224353106	4
	10 A	7210.3200.9	4008224353113	4
	13 A	7213.3200.8	4008224353120	4
	16 A	7216.3200.7	4008224353144	4
	20 A	7220.3200.0	4008224353151	4
	25 A	7225.3200.5	4008224353168	4
	32 A	7232.3200.7	4008224353175	4
	 <p><b>Leitungsschutzschalter MCB, 1-polig</b> <i>Miniature Circuit Breaker MCB, 1-pole</i> 230/400 V AC</p> <p><b>K</b></p>	3 A	7203.0300.7	4008224497114
6 A		7206.0300.6	4008224163156	12
10 A		7210.0300.9	4008224163163	12
16 A		7216.0300.7	4008224163170	12
20 A		7220.0300.0	4008224163187	12
25 A		7225.0300.5	4008224163194	12
32 A		7232.0300.7	4008224163200	12
 <p><b>Leitungsschutzschalter MCB, 2-polig</b> <i>Miniature Circuit Breaker MCB, 2-pole</i> 400 V AC</p> <p><b>K</b></p>	2 A	7202.2300.8	4008224497145	6
	3 A	7203.2300.1	4008224497152	6
	4 A	7204.2300.4	4008224497169	6
	25 A	7225.2300.9	4008224163699	6
	32 A	7232.2300.1	4008224163705	6
 <p><b>Leitungsschutzschalter MCB, 3-polig</b> <i>Miniature Circuit Breaker MCB, 3-pole</i> 400 V AC</p> <p><b>K</b></p>	2 A	7202.3300.5	4008224497190	4
	3 A	7203.3300.8	4008224497206	4
	4 A	7204.3300.1	4008224497213	4
	10 A	7210.3300.0	4008224163972	4
	16 A	7216.3300.8	4008224163989	4
	20 A	7220.3300.1	4008224163996	4
	25 A	7225.3300.6	4008224164009	4
	32 A	7232.3300.8	4008224164016	4