


PRODUCT-DETAILS

TC5347AX

2/4WAY MTG BASE 1.1X1.1IN BLK ADH



General Information

Extended Product Type	TC5347AX
Product ID	7TCG009800R0008
EAN	5414363058991
Catalog Description	2/4WAY MTG BASE 1.1X1.1IN BLK ADH
Long Description	Four-Way and Two-Way Mounting Base With Open Leg Design, Black Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Weather and UV Resistant, Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.7mm (0.34 Inches), Self-Adhesive Mounting Method, 100 Pack

Ordering

EAN	5414363058991
UPC	786210549514

Dimensions

Product Net Length	0, mm
--------------------	-------

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	15.4 in

	391 mm
Package Level 2 Height	11 in
	279 mm
Package Level 2 Depth / Length	23.6 in
	599 mm

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19980621
Material	Nylon/Polyamide 6.6 Weather Resistant
Mounting Type	Self-Adhesive
Number of Batteries	0
Process Temperature Rating	-32 to +150 °F
Product Name	CABLE TIE 1 BLK MTG BASE-ADH
Product Type	Mounting Base
Special Functions	Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC5347AX
Instructions and Manuals	TC5347AX
REACH Declaration	9AKK107992A8789
RoHS Information	9AKK107991A8363

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

