



DELTA, shutter/blind control

Model		
product brand name	DELTA	
product designation	Shutter/blind control	
Supply voltage		
operating voltage rated value	230 V	
supply voltage frequency		
• minimum	50 Hz	
• maximum	60 Hz	
Breaking Capacity		
switching capacity current	5 A	
Main circuit		
operational current rated value	5 A	
Relay contacts		
switching voltage of relay contacts rated value	250 V	
Product details		
product component extension input	No	
Number		
number of motors connectable	1	
Connections		
type of electrical connection	Max. 2.5 mm²	
Mechanical Design		
width	47.5 mm	
depth	20 mm	
length	47.5 mm	
fastening method	screw fixing	
Environmental conditions		
ambient temperature during operation		
• minimum	-10 °C	
• maximum	55 °C	
Approvals Certificates		
General Product Approval	other	Environment



[Miscellaneous](#)



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TC1272>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TC1272>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TC1272

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/26/2025 

