

BZ30 - Bizweld Trousers

Collection: Bizweld™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizweld Work: 100% Cotton

Outer Carton: 24

Product information

Designed to give maximum protection and comfort to the wearer, the Bizweld Trousers will keep you safe. The garment has twin stitched seams for extra strength and side pockets with a conveniently placed rule pocket for quick and easy accessibility.

Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM², ATPV 10.9 CAL/CM²)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM² (HAF = 80.4%))



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Side pockets
- Rule pocket
- Durable, strong and long lasting brass zip
- Twin-stitched seams for extra durability
- Available in sizes from XS to 5XL
- 40+ UPF rated fabric to block 98% of UV rays
- 3 pockets for ample storage
- Half elasticated waist for a secure and comfortable fit
- CE certified

BZ30 - Bizweld Trousers

Commodity Code: 6203421100

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777_12872_03_E00_00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
BZ30BKRS	Black	43.0	28.0	46.0	0.5600	0.0554	5036108211067	15036108696939
BZ30BKRM	Black	43.0	28.0	46.0	0.6800	0.0554	5036108211050	15036108696922
BZ30BKRL	Black	43.0	28.0	46.0	0.7200	0.0554	5036108211043	15036108696915
BZ30BKRXL	Black	43.0	28.0	46.0	0.6600	0.0554	5036108211074	15036108696946
BZ30BKRXXL	Black	43.0	28.0	46.0	0.7600	0.0554	5036108211081	15036108696953
BZ30BKRXXXL	Black	43.0	28.0	46.0	0.7800	0.0554	5036108211098	15036108696960