

FEATURES

- Opal white diffuser
- Polycarbonate yellow base
Cable entry at one end through a fitted IP65 gland
- Mounting brackets supplied
- Integrated LED tray

RS PRO 30 W LED Ceiling Light, 240 V Rectangular Single Batten, Anti-corrosive, 1.524 m Long, IP65

RS Stock No.: 145-5914



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS Pro LED 30W luminaire light fitting has a unique LED tray, no tube is required making it a more durable fitting. The LED luminaire is 5ft (610mm) and has an IP65 rating making it waterproof and ideal for environments which have high humidity. Luminaires are light fixtures and are the physical structures that will hold the bulb and help create the light by allowing the electricity to pass into the lamp. Ceiling lights are found in homes, offices, factories, and many other buildings and structures

General Specifications

Type	Single Batten
Colour Tone	Cool Daylight
Lamp Type	LED
Colour Temperature	6000K
Life Hours	30000h
Anti-Corrosive	Yes
PIR Included	No
Applications	Ceiling lights are a very common type of light fixture which can be fitted to the ceiling in: Industrial areas; Multi-storey car parks; Workshops, warehouses and factories; Garages
Dimmable	No

Electrical Specifications

Wattage	30W
Voltage Rating	240V

Mechanical Specifications

Length	1.524m
Beam Angle	120°
Lumen Output	2500lm

Operation Environment Specifications

Temperature	-15°C to 50°C
-------------	---------------

Protection Category

IP Rating	IP65
-----------	------

Approvals

Compliance/Certifications	RoHS Certificate Of Compliance
---------------------------	--------------------------------



