

3-Wire *picofast*® Cordsets, Threaded Coupling Nut

- Straight Female Connectors
- NEMA 1, 3, 4, 6P and IEC IP 67 Protection
- 125 VAC/VDC, 4 A



Housing Style	Part Number	Cable	Features	Pinout
PKG ..M** 1.366 [34.7] 0.354 [9.0] M8x1 PKG V ..M** 1.366 [34.7] 0.378 [9.6] M8x1	PKG 3M-*	AWM PVC Yellow 3x24 AWG 105°C 4.4 mm OD Cable #RF50642-*M [†]	<i>flexlife</i> ®	1. BN 3. BU 4. BK
	PKG 3M-*/S90	AWM PUR Black 3x24 AWG 105°C 4.4 mm OD Cable #RF50587-*M [†]	<i>Cut/Abrasion Immune</i>	
	PKG 3M-*/S90/S101	AWM PUR Black 3x26 AWG 105°C 4.4 mm OD Cable #RF50723-*M [†]	<i>Cut/Abrasion Immune, flexlife-10, High Flex - Over 10 Million Cycles</i>	
	PKG 3M-*M/S90/S618	AWM PUR Black 3x24 AWG 105°C 4.4 mm OD Cable #RF50601-*M [†]	<i>Cut/Abrasion Immune, EMI/RFI Protection</i>	
	PKG 3M-*M/S760	AWM PVC Black 3x24 AWG 4.4 mm OD Cable #RF50585-M [†]	<i>flexlife</i>	
	PKG 3M-*/XOR	PVC Orange 3x24 AWG 80°C, 250° C short term 4.4 mm OD Cable #RF04449-*M [†]	<i>Weld Flash Immune, High Temp. Immune</i>	

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters.

** Standard coupling material is nickel plated brass.. "PKG..M"; "PKG V..M" indicates 316 stainless steel.

[†] See Section N for *reelfast*® cable information.