

Datasheet

**RS Pro Non-Fused Terminal Block, 3 Way/Pole, Screw  
Terminals, 22 to 12 AWG Free Hanging, Panel Mount, PA**  
RS Stock No: **763-8129**



## Product Details

Rs Pro non-fused terminal block in black, has polyamide housing and M3.5 steel nickel plated screws. This block with 3 ways, features screw termination. This terminal block with 22 to 12 AWG wire, supports free hanging and panel mounting types. The terminal block with 750 V voltage rating, has brass contact with tin plating.

## Features and Benefits

- 0.8 Nm maximum torque
- Operating temperature of -40 to +105°C
- 9.5 mm pitch
- 15 A current rating



ENGLISH

### Specifications:

Contact Material	Brass
Contact Plating	Tin
Current Rating	15 A
Material	Polyamide Housing
Maximum Operating Temperature	+105°C
Minimum Operating Temperature	-40°C
Mounting Type	Free Hanging, Panel Mount
Number of Ways	3
Pitch	9.5 mm
Termination Method	Screw
Voltage Rating	750 V
Wire Size	22 to 12 AWG
Colour	Black
Dimensions	45.5 x 21.6 x 13 mm
Screw Size	M3.5
Standards Met	RoHS, CE (BS EN 6.998)