

### Main

Range	Mureva
Product or component type	Data socket
Device application	Communication
Device presentation	Complete product
Data socket type	RJ45 RJ45 - 8 contacts
Box colour tint	White
Cover frame colour tint	White
Cover plate colour tint	White
Provided equipment	Protective flap Label holder





### Complementary

Communication network category	6
Socket number	1
Cable shielding type	S/FTP
Device mounting	Flush
Installation direction	Straight
Material	ABS thermoplastic
Fixing mode	Clip-in
Connections - terminals	Click
Height	84 mm
Width	84 mm
Depth	40 mm

### Environment

IP degree of protection	IP55
IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>