

## Features

- Lightweight and flexible
- BfR, kap XXI, kat. 2.  
EU Reg. No.:  
1935/2004 &  
2023/2006
- Blue colour
- 20m length

## RS PRO Hose Pipe

RS Stock No.: 486-596, 486-625, 486-665



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Blue, smooth, flexible hose with BfR-approved inner rubber layer. For hot and cold beverages, e.g. beer, wine, fruit juice and milk. Inner and outer surfaces are resistant to vegetable and animal oils.

It is recommended that new hoses be flushed with 5% soda solution before use.

Flushing after use is also recommended.

It is commonly installed using stainless steel connectors or hose clamps.

## General Specification

Brand	RS PRO
Features	Flexible
Materials	NBR/PVC
Reinforcement	PVA
Colour	Blue
Length	20m
Suitable Applications	Food
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-20°C
Maximum Working Pressure	20 bar
Hose Pipe Action	Transfer
Standards Met	BfR, kap XXI, kat. 2. EU Reg. No.: 1935/2004 & 2023/2006
Bend Radius	100mm

## Products in series

Stock No.	Length	Inner Diameter	Outer Diameter	Colour
486-596	20m	13mm	24mm	Blue
486-625	20m	19mm	31mm	Blue
486-665	20m	25mm	39mm	Blue