

STOFLEX HOSE ASSEMBLIES ANTI-STATIC RUBBER PAINTING

STOFLEX anti-static rubber hose extension and PREVOS1 swivel safety quick coupler



Part number	Length (m)	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)	Profile
RAL SISW810	10.00	-15.00 / 70.00	12.00	2,28	ISO 6150B
RAL SISW1012	12.50	-15.00 / 70.00	12.00	3,2	ISO 6150B
RAL SESW810	10.00	-15.00 / 70.00	12.00	1,9	EUROPEAN
RAL SESW910	10.00	-15.00 / 70.00	12.00	2,06	EUROPEAN
RAL SESW912	12.50	-15.00 / 70.00	12.00	2,5	EUROPEAN
RAL SESW1012	12.50	-15.00 / 70.00	12.00	2,6	EUROPEAN
RAL SCSW810	10.00	-15.00 / 70.00	12.00	0	ISO 6150C
RAL SCSW1012	12.50	-15.00 / 70.00	12.00	2,7	ISO 6150C

Part number	Ø int/ext (mm)
RAL SISW810	8.00 / 15.00
RAL SISW1012	10.00 / 18.00
RAL SESW810	8.00 / 15.00
RAL SESW910	9.00 / 16.00
RAL SESW912	9.00 / 16.00
RAL SESW1012	10.00 / 18.00
RAL SCSW810	8.00 / 15.00
RAL SCSW1012	10.00 / 18.00