



POLIFAN flap disc PFF 125x22.23 mm flat Z80 Universal Line PSF STEELOX steel/stainless steel

POLIFAN flap disc PFF 125x22.23 mm flat Z80 Universal Line PSF STEELOX steel/stainless steel

Item number: [67668125](#)

EAN: [4007220512531](#)

The entry-level range Universal Line PSF includes robust tools for processing the most common materials. Universal Line PSF tools achieve good results with high economic efficiency.

POLIFAN flap disc for steel and stainless steel (INOX) with aggressive stock removal rate and good tool life.

Technical information

Abrasive	Zirconia alumina Z
Dia. external	125 mm
Dia. hole	22.23 mm
Grit size	80
Max. RPM	12200 RPM
Mounting system	Centre hole
Shape	PFF / A / T27
Version	No information

Advantages

- ✓ Fast work progress and high economic efficiency thanks to the good stock removal rate.
- ✓ Good tool life.
- ✓ Also suitable for low-power angle grinders.

Materials that can be worked

- ✓ Stainless steel (INOX)
- ✓ Steel

Applications

- ✓ Chamfering
- ✓ Deburring
- ✓ Step-by-step fine grinding
- ✓ Surface grinding
- ✓ Work on weld seams

Drive types

- ✓ Angle grinder
 - ✓ Drive spindle
-



August Rüggeberg GmbH & Co. KG
Hauptstraße 13
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com