

# Eaton 12TDLEJ40

Catalog Number: 12TDLEJ40

Eaton Bussmann series medium voltage DIN fuse, 40 A, AC 12 kV, 2", 51 x 292 mm, backup, DIN, with striker

General specifications



| Product Name                                  | Catalog Number       |
|-----------------------------------------------|----------------------|
| Eaton Bussmann series medium voltage DIN fuse | 12TDLEJ40            |
|                                               | EAN                  |
|                                               | 5027590516440        |
| UPC                                           | Product Length/Depth |
| 051712186094                                  | 292 mm               |
| Product Height                                | Product Width        |
| 54 mm                                         | 51 mm                |
| Product Weight                                | Compliances          |
| 1574 g                                        | DIN 43625            |
|                                               | VDE 0670-4           |
|                                               | IEC 60282-1          |
| Certifications                                |                      |
| UL                                            |                      |
| VDE                                           |                      |

## Product specifications

### Used with

270303 Fuse clip

A3354710 Fuse clip

### Type

Fuse

### Special features

Back-up, Transformer protection, Indoor or outdoor use

### Application

transformer protection

indoor or outdoor use

### Amperage Rating

40 A

### Fuse indicator

With Striker

### Fuse size

51 x 292 mm

### Breaking capacity

63 kA

### Installation technique

Air

### Performance Cat According To IEC 60282-1

Back-up

### Product application

Primary side transformer protection

### Rated frequency - max

50 Hz

### Rated frequency - min

50 Hz

### Release characteristic

Other

### Standard

DIN

### Utilization category

Other

### Voltage type

## Resources

### Technical data sheets

[720105 17.5kV DIN medium voltage fuses](#)

[720104 12kV DIN medium voltage fuses](#)

[720106 24kV DIN medium voltage fuses](#)

AC

With striker

Yes

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Pre arc (I<sup>2</sup>T)

2.4 x 1000

Resistance

17.2 Ohms

Watt losses

36 W

Fuse diameter

51 mm

Color

Brown

Interrupt rating

63 kAIC

Construction size

51 x 292 mm

Mounting method

Clip-in

Packaging type

Standard

Quantity

1

Voltage rating

12 kV

Fuse type

TDLEJ



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)