

Product data sheet

Specifications



Spacial SF front plinth - 100x400 mm

NSYSPF4100

Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or component type	Plinth front
Anwendung	Multi-purpose
Nennmaße des Gehäuses	-
Device composition	fixing elements 4 corner cover 1 front panel 1 rear panel 4 corner
Range compatibility	Spacial SF Spacial SM
Mounting support	Plinth side panels

Complementary

Fixing mode	By fixing element - on structure location
Colour	Grey (RAL 7022)
Surface finish	Epoxy-polyester powder
Permanent permissible load	1300 kg
Height	100 mm
Width	400 mm nominal:

Environment

IP degree of protection	IP30 (complete plinth)
IK degree of protection	IK10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.531 kg
Package 1 Height	11.0 cm
Package 1 width	20.5 cm

Package 1 Length	41.5 cm
------------------	---------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

REACH free of SVHC	Yes
--------------------	-----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

Mercury free	Yes
--------------	-----

RoHS exemption information	Yes
----------------------------	---------------------

China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Contractual warranty

Warranty	18 months
----------	-----------
