



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**
Housing Type: **Tab Housing**
Number of Positions: **6**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Product Type	Terminal Housing
Style Code	C
Sealable	No
Housing Type	Tab Housing
Insulated	No

Configuration Features

Number of Positions	6
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	With



Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention Type	Locking Lance
Mating Alignment	With
Crimp Terminal Housing Mounting Style	Panel Mount

Housing Features

Housing Material	Polyamide
Centerline (Pitch)	5 mm[.196 in]

Dimensions

Length	30.5 mm[1.2 in]
--------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	200
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability












Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 9-927742-2 2POS FASTIN FASTON HOUSING	 TE Part # 964492-2 2 POS FASTIN/ON HOUSING PANEL MOUNT	 TE Part # 5-964492-5 FASTIN FASTON HOUSING 5POS	 TE Part # 1241857-5 5 POS FASTIN/ON HOUSING PANEL MOUNT
 TE Part # 9-927742-4 4POS FASTIN FASTON HOUSING	 TE Part # 9-927742-3 FASTIN FASTON HOUSING 3POS	 TE Part # 7-927742-6 6 POS. FASTIN-FASTON* TAB HSG RAST5	 TE Part # 927742-4 4 POS FASTIN/ON HOUSING PANEL MOUNT
 TE Part # 1-927742-6 6 POS. FASTIN-FASTON* TAB HSG RAST5	 TE Part # 5-1241967-6 6POS. FASTIN-FASTON* TAB HSG, RAST5	 TE Part # 5-927742-6 6 POS FASTIN/ON HOUSING PANEL MOUNT	 TE Part # 6-927742-6 6 POS FASTIN/ON HOUSING PANEL MOUNT
 TE Part # 9-1241857-5 5POS. FASTIN-FASTON* TAB HSG, RAST5	 TE Part # 927742-5 5 POS FASTIN/ON HOUSING PANEL	 TE Part # 927742-7 7P FF FLACHSTGH6,3	

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)




Connector Contacts(12)



Crimp Terminal Housings(41)




Insertion & Extraction Tools(1)




PCB Headers & Receptacles(424)



Rectangular Connector Housings(1)



Standard Edge Connectors(36)



Standard Rectangular Connectors(112)




Wire-to-Board Connector Assemblies & Housings(212)



Wire-to-Board Connector Contacts(2)

Customers Also Bought




TE Part #3-1534796-9
AMP DUOPLUG MK2 CONNECTOR 9P



TE Part #6-1241961-2
STD TIM HOUSING MKII 2POS



TE Part #1955415-1
3P CLUSTER BLOCK HOUSING




TE Part #1534075-4
MULTIF.ASSY MK2 4P



TE Part #1534077-3
MULTIFIT MK2ASSY 3P,IR



TE Part #1718044-3
RAST2.5 W2W Crimp-IDC 2pos Motor Mnt



TE Part #8-1534798-6
AMP DUOPLUG MARK II CONNEC. SEL

Documents



Product Drawings

6 POS FASTIN/ON HOUSING PANEL MOUNT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_927742-6_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_927742-6_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_927742-6_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTIN_FASTON_Product_Line

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English

VDE Certificate

English

VDE Certificate

English