

eco!Booster TR 040

eco!Booster with 50% higher area performance than the Kärcher power nozzle; ideal for delicate surfaces. For cold and hot water high-pressure cleaners (nozzle size 040).



Order no. **2.113-086.0**

Technical data

EAN code		4066529118837
Pressure	bar	max. 300
Temperature	°C	max. 85
Nozzle size		40
Connection thread		EASY!Lock
Weight incl. packaging	kg	0.5



50% higher cleaning performance compared to the flat jet

- Thorough, fast and more sustainable cleaning.

50% higher water efficiency*

- Saves water.
- * Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

50% higher energy efficiency*

- Saves energy.
- * Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

COMPATIBLE MACHINES

- HD 7/15 G
- HD 7/17 M
- HD 728 B Cage
- HD 8/20 G
- HDS 1.7/12 U Ed
- HDS 3.5/30-4 M Ea
- HDS 5/13 U
- HDS 7/16 C