



### Main

Range of product	Harmony XAP
Product or component type	Die-cast empty control station
Device short name	XAPG
Product destination	For Ø 22 mm control and signalling units
Number of cut-out	5 cut-outs
Colour of base of enclosure	Grey RAL 7032
Colour of cover	Grey RAL 7032
Material	Zinc alloy
Cable entry	1 hole with blanking plug for cable gland with ≤ 14 mm 1 hole without blanking plug for cable gland with ≤ 14 mm
Product mounting	Flush mounting
IP degree of protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010

### Complementary

Number of vertical rows	1
-------------------------	---

### Environment

Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Electrical shock protection class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications