



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Time switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Grey (RAL 7035)
Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand

Complementary

Poles description	1P + N + E
Device mounting	Surface
Plug, socket, control station shape	Straight Angled
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	16 A
Protection type	Without protection
Marking	Without marking
Height	101 mm
Width	101 mm
Depth	102 mm
Net weight	0.6 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
Outlet standard	Industrial
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133 AS/NZS 3123

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	598 g
Package 1 Height	116 mm
Package 1 width	108 mm
Package 1 Length	109 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile