

PARATHOM MR11 20 36° 2.6 W/827 GU4

PARATHOM MR11 12 V | Low-voltage LED reflector lamps MR11 with retrofit pin base



Areas of application

- Display cabinets and shop windows
- Museums, art galleries
- Exhibition rooms
- Residential interiors
- As a downlight for marking walkways, doors, stairs, etc.
- Outdoor applications only in suitable luminaires

Product benefits

- Long lifetime of up to 15,000 h
- Low energy consumption
- Easy relamping thanks to compact design and GU4 base

Product features

- Professional LED alternative to halogen MR11 lamps
- Compatible with many common electronic control gears (see also compatibility list)
- Mercury-free lamps



Technical data

Electrical data

Rated wattage	2.60 W
Nominal wattage	2.60 W
Nominal voltage	12.0 V
Claimed equiv. conventional lamp power	20 W
Operating frequency	50...60 Hz
Power factor λ	> 0.50


Photometrical data

Luminous intensity	400 cd
Nominal luminous flux	184 lm
Rated luminous flux	184 lm
Color temperature	2700 K
Color rendering index Ra	≥ 80
Light color (designation)	Warm White
Standard deviation of color matching	≤ 6 sdcn
Nominal useful luminous flux 90°	184 lm
Rated useful luminous flux 90°	184 lm
Rated peak intensity	400 cd
Nom. useful luminous flux 120°	200 lm
Rated useful luminous flux 120°	200 lm

Light technical data

Beam angle	36 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s
Nominal beam angle	36 °
Rated beam angle (half peak value)	36.00 °

Dimensions & weight



Overall length	38.0 mm
Diameter	34.7 mm
Outer bulb	MR35
Length	38.0 mm

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000
Lumen main.fact.at end of nom.life time	0.70

Additional product data

Base (standard designation)	GU4
Mercury content	0.0 mg
Mercury-free	Yes
Appropriate disposal acc. to WEEE	Yes
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value

Capabilities

Dimmable	No
----------	----

Certificates & standards

Energy efficiency class	A+
-------------------------	----

Product datasheet

Energy consumption	3 kWh/1000h
--------------------	-------------

Country specific categorizations

ILCOS	DRR-2,6/827-12-GU4-35/36
Order reference	PMR112036 2,6W/

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899954977	PARATHOM MR11 20 36° 2.6 W/827 GU4	Shipping carton box 10	188 mm x 75 mm x 55 mm	0.78 dm ³	258.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For further products and actual information concerning LED lamps see

▶ www.ledvance.com/ledlamps

For Guarantee see

▶ www.ledvance.com/guarantee

Further information see

▶ www.ledvance.com/low-voltage-ledlamps

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.