

Professional Extension Cable VN 1100 IP 44, 10 m black H07RN-F 3G1,5

For use on construction sites in accordance with DGV 203-006 (formerly BGI 608) and permanent outdoor use.



**MADE IN
GERMANY**

5 YEARS
MANUFACTURER
GUARANTEE



Product number
EAN

9161100110
4007123687763

DESCRIPTION

- With extra robust earthing contact plug and coupling with sealing cap.
- UV-resistant plug and coupling with kink protection and cable seal.
- The RN cable is very robust, oil-resistant and particularly suitable for professional use.
- Category 2 equipment (K2 DGV 203-005): Used for harsh operating conditions with high mechanical, physical and chemical impacts.

TECHNICAL DATA

Cable quality	Rubber-Neoprene	Connection	Earthed plug/Earthed coupling
Cable length	10 m	Plug system plug	Type E and F (Protective contact with earth hole)
Cable designation	H07RN-F 3G1,5	Plug system socket/ coupling	Type F (Protective contact)
Cable colour	black	Degree of protection (IP)	IP44

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	1.4 kg
Weight of product (without packaging)	1.39 kg	Dimension LxWxH (incl. packing)	21 cm x 21 cm x 7 cm
Dimension LxWxH (without packing)	21 cm x 21 cm x 7 cm		

SCOPE OF DELIVERY

Professional Extension Cable VN 1100 IP44