

## Product information

# 14.4V 10MM 2 SPEED DRILL DRIVER



Satisfying the professional's needs

### 6281DWPE

Voltage	14.4 v
No Load Speed	H: 0 - 1300 / L: 0 - 400 rpm
Torque Settings; S/H Nm	16; 20/36
Battery Type	Ni-Cad
Charging Time	30 min
Battery Quantity (1.3Ah)	2
Vibration: Drilling	2.5 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)
Net weight	1.6 kg



- Compact & Lightweight
- Ideal for working in confined space
- Keyless Chuck
- Reversible
- Variable speed

Details correct as of: 8-10-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makitauk.com](http://www.makitauk.com)