

Eaton 248441

Catalog Number: 248441

Eaton Distribution parts. Shunt release, up to 125A, 12-60V, 1.5HP

General specifications



Product Name

Eaton Distribution parts

Catalog Number

248441

EAN

4015082484415

Product Length/Depth

80 mm

Product Height

75 mm

Product Width

39.1 mm

Product Weight

0.159 kg

Compliances

RoHS conform

Certifications

EN45545-2

IEC 61373

Product specifications

Used with

Shunt releases

Accessory

Accessory for miniature circuit breaker

Type

Accessory

Accessory for miniature
circuit breaker

Application

Switchgear for industrial and advanced commercial applications

Accessory/spare part type

Shunt release

Mounting method

For fitting on left to: AZ

Additional equipment required

Shunt release (for power circuit breaker)

Ambient operating temperature - max

40 °C

Ambient operating temperature - min

-5 °C

Assembly width

1.5 TE

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

1

Number of poles at main contact unit - max

1

Number of switches (fault signal)

0

Voltage type

AC

Functions

Shunt release (for power circuit breaker)

Resources

Declarations of conformity

[DA-DC-03_Z-LHASA](#)

Drawings

[eaton-dimensions-mas-lhasa.eps](#)

[eaton-dimensions-ma-lhasa.jpg](#)

eCAD model

[ETN.Z-LHASA_24.edz](#)

Installation instructions

[IL019166ZU](#)

mCAD model

[z_lhasa_230.stp](#)

[z_lhasa_230.dwg](#)

Wiring diagrams

[Z7_asa](#)

Device fitting

Miniature circuit breaker (MCB)

Rated operational voltage (Ue) - max

24 V

Rated switch current

18 A

Suitable for current of main contact unit - max

14 A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)