
KERN **FCB-A01**

Rechargeable battery pack internal (EU)



Trade number 85075000

Pictograms

STANDARD



Category

Brand	KERN
Product category	Balance
Product group	Rechargeable battery

Power Supply

Supplied power supply	Power supply unit
Input voltage power supply / power [Max]	100 - 240 V ~ 50/60 Hz 0.5 A
Battery / accumulator type	NiMH
Battery connection	Plug-in terminals
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	10 h
Rechargeable battery charging time	10 h
Battery/Accu connected	not connected, enclosed

Environmental conditions

Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	92×70×68 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,25 kg
Shipping weight	0,24 kg
Shipping volume weight	0,1 kg

Product information

GTIN/EAN number	4045761085268