

Datasheet

Product Name: UL1430 24AWG
Product Discription: UL1430 24AWG
Specification No.:
Customer's Name:

					Customer's Name:				
Description					Construction				
Rated V	oltage:		300V		Conductor	Stranded Tinned Co	ppper		
Rated T	emperature:		105℃		Size(AWG)	24			
Referen	ce Standard:	UL7	58,UL1581		Construction(±0.008mm)	11/0.16			
Cross Section					Stranded Dia.(mm)Ref.	0.6			
					Insulation Material	XLPVC			
					Insulation Color	ANY COLOR			
					Ave Thickness(mm)	0.38			
					Insulation Dia.(±0.10mm)	1.40			
Marking					Remark:				
					8739933 Red	8739942 Blu	e 8739955 Grey	8739964 Violet	
AWM XLPVC 1430 24AWG 105°C 300V Horizontal flam					8739936 Black	8739945 Wh	nite 8739958 Yellow		
C¶ AWM XLPVC 105°C 300V I A FT2 E214859 YANG TAI					8739939 Brown	8739949 Gre	een 8739951 Orange		
					Characteristics			Customer Approve	
Applications					Test Item		Standard Value		
For internal wiring of electronic and electrical equipment					Test Material		XLPVC(ROHS)		
					Insulation resistance(20℃ MΩ*m		1000		
					Vol. Tesr(AC.V.60S) (V)		2000	Seal & Stamp	
					Flammability Test		Horizontal flame		
					Max.DC Resistance(20℃ Ω/km)		94.2(MAX)		
Version	Description	Drawn by	Approved by	Date					
0	New document iss	ue Huang	Jason	14/04/2015					
								Signature:	
								Date:	

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.