



# 150 mm Adjustable Wrench - 1 pc

## ADJUSTABLE WRENCHES

- Precision adjustment screw with accurate threads and tight tolerances. The jaws won't back off during use.
- Chrome plating for best-in-class rust protection and increased durability.
- Ergonomic rounded handle design for a comfortable fit in the hand and less pressure points on the palm.
- Slim head design for reaching into tight spaces.
- Parallel jaws won't slip or damage finish surfaces.
- Permanent lasered inch and mm markings for accurate adjustment
- 8" adjustable wrench (48227508) has an extra wide jaw of 38 mm for increased jaw capacity in confined environments.
- Lanyard hole.
- Available sizes: 150mm, 200mm, 200mm (wide), 250mm, 300mm, 380mm.
- Available packs: Twin, Triple.



|                                    |                      |
|------------------------------------|----------------------|
| Article Number                     | 48227406, 4932499518 |
| Jaw opening capacity for pipe (mm) | 24.5                 |
| Jaw thickness [mm]                 | 11.5                 |
| Pack quantity                      | 1                    |
| Tip thickness [mm]                 | 7,7                  |
| Total length (mm)                  | 150                  |
| Total length [inch]                | 6                    |
| Weight (g)                         | 186                  |