



EG320 Professional glue gun

Designed to answer professional users, EG320 is a well balanced glue gun - compact size and light weight - for easy use and operation in narrow spaces.

EG320 allows glue output up to 1 Kilo per hour. Its 4 fingers trigger reduces fatigue during intensive use and provides good comfort.

Applications : PVC, Cables and tiles sealing, Electronics and electrics, Furniture and wood working, manual and corrugated carton sealing, trade exhibits and installation...

Features:

- Light weight and compact size for operating with smaller hands
- Interchangeable nozzle according to applications
- Smooth-4 fingers trigger for best comfort and reducing effort required
- Mobile and fixed stand for best efficiency
- Main switch ON/OFF

Specifications:

- Power rating : 120W
- Working voltage : 220-240V
- Glue Output: 25g/min – 1.000g/h
- Heating time at 195°C: 3 min
- Cord length: 1.75m
- Nozzle : Ø 3.0mm
- Regulation : Self-regulated
- Temperature setting : 195°C
- Dim : 205*240*45mm
- Weight : 0.48kg



Description

EG320 UK plug

Packaging

Cardboard box

Art. No

5000714

EAN

4051661022562

Outer

5 pcs

ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com

Rapid®
SVENSK EFFIXITY