




Datasheet

Stock No: 331-3630

ENGLISH

# RS Pro 2.4 → 4 A Motor Protection Switch

## Product Details



### Motor Protection Switches - XL-2000-01

- Overload protection compensated -5 to +40°C
- Lockable in 'OFF' position
- Short circuit protection, therefore, no back-up fuse protection is required where the prospective fault level is less than the breaking capacity of the unit
- Expected life cycles  $0.1 \times 10^6$
- Maximum switching frequency 40 operations/hour
- Ambient temperature (min/max) -25 to +55°C (open) and up to +40°C (closed)

### Standards

IEC 947-2, IEC 9474.

## Specifications:

Current Range:	2.4 → 4 A
Terminal Type:	Screw
Length:	80mm
Width:	45mm
Depth:	73.5mm
Dimensions:	80 x 45 x 73.5 mm
For Use With:	MS25 Series
Series:	XL2000