



Cold



Medium Duty

Waterproof cold-resistant gloves, keeping hands warm and dry with grip and flexibility

- **Specialized defenses:** ActivArm® 97-681 cold weather work gloves feature a PVC foam coating that remains flexible in temperatures as low as -25°C/-15°F, providing frostbite protection and moderate cut resistance
- **Advanced protection:** Designed with a RIPEL™ Technology liquid-repellent surface barrier, these work gloves are also liquid-proof, for warm, dry hand protection
- **Elevated comfort:** ActivArm® 97-681 safety gloves combine a PVC-coated nylon exterior with a soft, insulative acrylic interior, for comfort and warmth
- **Optimized thickness levels:** They are also thin enough to handle small components with dexterity, without compromising hand safety
- **Food handling compliance:** Ideal food handling gloves, they meet relevant food processing and hygiene standards



Industries

- Food Processing
- Infrastructure Maintenance
- Oil and gas

Applications

- Cold Storage
- Sanitation
- Drilling / Extraction
- Production Services / Processing

Key Features

- **PVC coating:** Grip and flexibility even in the coldest temperatures
- **RIPEL™ Technology:** For truly waterproof industrial gloves
- **Two-layer design:** Protecting hands while providing comfort and warmth

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



2231B

EN 511



221



Technologies



RIPEL™

Liquid Repellence Technology

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 97-681	Finishing: Fully Coated Coating Material: PVC Liner Material: Acrylic, Nylon Cuff Style: Gauntlet	N/A	8, 9, 10, 11	250-285 mm; 9.84-11.22 inches	Blue	6 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.