



DCF885L2-XE

18 Volt XR Li-Ion Cordless Compact Impact Driver

Selling Proposition

- Ultra compact, light weight design allows for use in confined spaces
- Improved ergonomic design and rubber grip increase comfort
- All metal gearing for efficient power transmission and long tool life
- Aluminium front housing provides greater heat dispersion increasing motor life
- Intelligent trigger allowing total control over all applications
- 6.35mm 'drop in' keyless hex driver allows for quick, one handed fitment
- Bright white LED with delay feature for improved visibility and flashlight functionality

Standard Equipment

- Multi-voltage charger
- 2 slide pack batteries
- heavy duty carrying case

Warranty Specifications

- 3 Year Limited Warranty (Terms and Conditions Apply)
- 1 Year Free Service Contract
- 30 Day No Risk Satisfaction Guarantee

Specifications	
Voltage	18 V
Battery Capacity	3.0 Ah
Bit Holder	1/4" (6.35mm)
Power Output	250 Watts
No Load Speed	2800 rpm
Impacts per Minute	3200 ipm
Max Torque	155 Nm
Max. Bolt Diameter	M12
Weight	1.6 kg
Length	141 mm