



Part Number : [2319644082](#)
Product Description : Micro-Lock Plus-to-Micro-Lock Plus Off-the-Shelf (OTS) Cable Assembly, 1.50mm Pitch, Single Row, 450.00mm Length, 8 Circuits, Black
Series Number : 231964
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings
[2319644082 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	231964
Description	Micro-Lock Plus-to-Micro-Lock Plus Off-the-Shelf (OTS) Cable Assembly, 1.50mm Pitch, Single Row, 450.00mm Length, 8 Circuits, Black
Application	Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Lock Plus-to-Micro-Lock Plus
Keyword	Micro-Lock Plus 1.5
Product Name	Micro-Lock Plus
Type	Discrete Wire Assembly
UPC	198930932055

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Cable Length	450.00mm
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes

Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Polyester
Net Weight	12.468/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	1.50mm
Plating min - Mating	0.800µm
Plating min - Termination	0.800µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	24

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.50mm Pitch, Micro-Lock Plus Vertical, Single Row, Surface Mount Headers	<u>225053</u>
1.50mm Pitch, Micro-Lock Plus Right-Angle, Single Row, Surface Mount Headers	<u>225054</u>

Use with Part(s)

Description	Part Number
1.50mm Pitch Micro-Lock Plus Female Crimp Terminals	<u>225051</u>