

product type designation

product description

PB BFOC Plug POF

BFOC connector

PROFIBUS Plastic Fiber Optic, BFOC connector, 1 pack = 20 units.



suitability for use

For assembling PB plastic fiber-optic cables for OLM/P..

transfer rate

transfer rate / with PROFIBUS

9.6 kbit/s ... 12 Mbit/s

interfaces

number of optical interfaces / for fiber optic cable

1

design of the optical interface / for network components or terminal equipment

BFOC connector

type of electrical connection / FastConnect

No

mechanical data

material / of the enclosure

metal

locking mechanism design

Bayonet

design, dimensions and weights

type of cable outlet

180° cable outlet

width

10 mm

height

10 mm

depth

10 mm

net weight

10 g

ambient conditions

protection class IP

IP20

product features, product functions, product components / general

product feature

- silicon-free

Yes

product component

- strain relief

Yes

standards, specifications, approvals

certificate of suitability

- RoHS conformity
- UL approval

Yes

No

- railway application in accordance with EN 50155

No

further information / internet links

internet link

- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Selection guide for cables and connectors
- to website: Image database
- to website: CAX-Download-Manager

<http://www.siemens.com/tia-selection-tool>
<http://www.siemens.com/simatic-net>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<https://sie.ag/2QdlxcP>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>

last modified:

9/7/2023 