

## Features

- Excellent abrasion and corrosion properties for increased durability.
- Good flexibility for ease of use.
- Manufactured from cadmium and silicone-free materials using a special low toxic, odourless PVC formulation that can reduce the taint of drinking water.
- EU No.10/2011 compliant for food contact applications.
- RoHS 3 compliant.
- Suitable for use with alcohol, petrol, oils, greases and solvents.
- Highly resistant to a wide range of acids and alkalis.
- Service temperature = -15°C to + 60°C.
- NSF51 + NSF61 approved for the transfer of drinking water

## RS PRO Hose Pipes & Flex Tubes

RS Stock No.: 0336821



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Clear PVC hose suitable for both low pressure food and industrial applications. It is manufactured from the highest quality, low-toxic materials to give excellent clarity, flexibility and durability over a wide temperature range.

Glass clear transparency for easy visibility.

- Excellent abrasion and corrosion properties for increased durability.
- Good flexibility for ease of use.
- Manufactured from cadmium and silicone-free materials using a special low toxic, odourless PVC formulation that can reduce the taint of drinking water.
- EU No.10/2011 compliant for food contact applications.
- RoHS 3 compliant.
- Suitable for use with alcohol, petrol, oils, greases and solvents.
- Highly resistant to a wide range of acids and alkalis.
- Service temperature = -15°C to + 60°C.
- NSF51 + NSF61 approved for the transfer of drinking water
- 

Applications:

- Medical
- Scientific
- Pharmaceutical
- Industrial

## General Specifications

Hose Pipe / Flexible Tube	Flexible Tube
Colour	Clear
Features	Flexible
Series	RS PRO C
Inner Diameter	4mm
Outer Diameter	6mm
Material	PVC
Hose Pipe Action	Transfer
Maximum Working Pressure	4bar
Suitable Application	Biopharmaceutical, Chemical, Food & Beverage, Medical
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Length	30m
Reinforced	No
Bend Radius	54mm
Standards Met	NSF 61; NSF 51