

FEATURES

- **Sintered Bronze Material:** Provides high durability and wear resistance, ensuring long service life.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying loads, maintaining performance under dynamic conditions.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, offering robust support in stationary applications.
- **Flanged Design:** Facilitates easy installation and secure fit, reducing the risk of misalignment.
- **ISO 2795 and ISO 9001:2008 Certified:** Meets international standards for quality and performance, ensuring reliability.

RS PRO 15.02 mm Flanged Plain Bearing

RS Stock No: 529-036



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable performance under both dynamic and static loads. Made from sintered bronze, it offers excellent durability and wear resistance, making it ideal for various industrial settings. The bearing's flanged design ensures easy installation and secure positioning.

General Specifications

Bore Size	15.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	21.05 mm
Width	25 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

