SanitPro Daily Cleaner CA 20 C eco!perform

Highly concentrated sanitary cleaner for manual maintenance cleaning. With innovative acid combination for effortless removal of mineral soiling. With EU Ecolabel certification.

pH value 2
in concentrate



Made in Germany

NTA-free

Properties

- Sanitary maintenance cleaning concentrate that can be used sparingly
- Removes limescale, soap and urine scale stains, as well as other typical soiling in sanitary areas
- Rinsed surfaces dry streak-free
- With easy-to-clean effect. Makes subsequent cleaning processes easier
- Pleasant, fresh scent
- Carries the European Ecolabel (EU Ecolabel)

Application areas

Building cleaning	Sanitary facilities
Hotels, gastronomy, catering	Sanitary facilities
Municipal	Sanitary facilities

Usage options

- Manual

Technical data

Container sizes	Packaging unit	Part number
1 l	12 Piece(s)	6.295-679.0
5 l	2 Piece(s)	6.295-680.0
200 l		6.296-163.0

We would be happy to advise you:

Application

Manual - using preconditioned mops

- Place required number of mops (10-15 mops) in the bucket.
- Pour cleaning solution over mops, 10-15 ml/mop.
- Close bucket, turn and allow to stand for 12 hours.
- Each cover cleans 20-25 m² depending on the degree of soiling.

Manual - using a mop

- Pour water into a bucket, add the required amount of cleaning agent.
- Remove coarse dirt from surface.
- Wet acid-sensitive surfaces if required.
- Apply cleaning agent to surface using a sponge or cloth.
- Scrub and rinse surface.
- Wipe surface dry if required.

Instructions for use

- Wear protective clothing when using the product.

Warnings and safety recommendations according to EC Directives

- Danger
- H290 May be corrosive to metals
- H315 Causes skin irritation
- H318 Causes serious eye damage
- P264 Wash thoroughly after handling.
- P280a Wear protective gloves / eye protection / face protection.
- P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P310 Immediately call a POISON CENTER/doctor.
- P362 + P364 Take off contaminated clothing and wash it before reuse.
- P406 Store in a corrosion resistant container / container with a resistant inner liner.

Further information

- Material Safety Data Sheet (MSDS)
- Quick Start

Dosage and yield

Contents	Cleaning method	Dosage	Soiling	Yield
1 l	Maintenance cleaning	0.3 – 1 %	mild	5000 m²
1 l	Maintenance cleaning	1 – 3 %	medium	2000 m²
1 l	Maintenance cleaning	3 – 8 %	strong	1000 m²

We would be happy to advise you: