

WP-STEEL S 21 - Protective hose

3240688

<https://www.phoenixcontact.com/in/products/3240688>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: Stainless steel 1.4301/AISI 304, degree of protection: IP40, color: silver, inside diameter: 18 mm, Total length: 10 m

Commercial data

Item number	3240688
Packing unit	1 m
Minimum order quantity	1 m
Sales key	BF7
Product key	AF7DSA
Catalog page	Page 597 (C-3-2019)
GTIN	4046356737432
Weight per piece (including packing)	999.9 g
Weight per piece (excluding packing)	999.9 g
Customs tariff number	83071000
Country of origin	DE

WP-STEEL S 21 - Protective hose



3240688

<https://www.phoenixcontact.com/in/products/3240688>

Technical data

Notes

Notes on operation	Protective hose length is measured stretched out; length tolerance $\pm 5\%$
--------------------	--

Product properties

Product type	Protective hose
Tensile strength GRP	500 N

Dimensions

Internal dimensions

Internal diameter	18 mm
-------------------	-------

Material specifications

Material	Stainless steel 1.4301/AISI 304
Components	halogen-free

Cable/line

Bending radius, dynamic	100 mm
Bending radius, static	40 mm
Tensile strength	500 N
Halogen-free	yes

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-200 °C ... 600 °C

WP-STEEL S 21 - Protective hose

3240688

<https://www.phoenixcontact.com/in/products/3240688>



Classifications

ECLASS

ECLASS-11.0	27430301
ECLASS-12.0	27430301
ECLASS-13.0	27430301

ETIM

ETIM 9.0	EC001179
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-STEEL S 21 - Protective hose



3240688

<https://www.phoenixcontact.com/in/products/3240688>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

WP-STEEL S 21 - Protective hose



3240688

<https://www.phoenixcontact.com/in/products/3240688>

Accessories

WP-SC BRASS 21 - Cable protection end sleeve

3241068

<https://www.phoenixcontact.com/in/products/3241068>



Cable protection end sleeve, material: Brass, nickel-plated, color: silver, inside diameter: 16.5 mm

WP-G BRASS IP40 PG16 - Protective hose screw connection

3241040

<https://www.phoenixcontact.com/in/products/3241040>



Cable gland made from brass with Pg thread, IP40 protection

WP-STEEL S 21 - Protective hose

3240688

<https://www.phoenixcontact.com/in/products/3240688>



WP-G BRASS IP40 M20 - Protective hose screw connection

3241047

<https://www.phoenixcontact.com/in/products/3241047>



Cable gland made from brass with metric thread, IP40 protection

WP-GT BRASS PG16 - Protective hose screw connection

3241026

<https://www.phoenixcontact.com/in/products/3241026>



Cable gland made from brass with Pg thread, rotatable, IP40 protection

WP-STEEL S 21 - Protective hose

3240688

<https://www.phoenixcontact.com/in/products/3240688>



WP-GT BRASS M20 - Protective hose screw connection

3241033

<https://www.phoenixcontact.com/in/products/3241033>



Cable gland made from brass with metric thread, rotatable, IP40 protection

WP-BASE HF 22 - Hose clamp

3240970

<https://www.phoenixcontact.com/in/products/3240970>



Hose clamp, material: Steel, galvanized, color: black/silver

WP-STEEL S 21 - Protective hose

3240688

<https://www.phoenixcontact.com/in/products/3240688>



WP-BASE A PG16 - Protective hose fixing bracket

3241079

<https://www.phoenixcontact.com/in/products/3241079>



Fixing bracket for protective sleeves, fixed with two screws

WP-BASE A M20 - Protective hose fixing bracket

3241084

<https://www.phoenixcontact.com/in/products/3241084>



Fixing bracket for protective sleeves, fixed with two screws

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in