

B0677 - Marathon S3 SRC

Collection: Record

Upper: Water Resistant Technical Textile

Lining: SmellStop Antiodor and Antibacterial*

Midsole: Fresh'n Flex

Toecap: SlimCap

Sole: Antifatigue AirTech + Tpu-Skin

Outer Carton: 10

Record

Record antifatigue footwear collection offers an answer to the demand for lightweight design.



Standards

UNI EN ISO 20345:2012 S3 (SRC)

Features

- Anti-static footwear
- Water resistant upper to prevent water penetration
- Non-magnetic - nickel and ferrous free
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Hydrocarbons resistant
- Electronic devices protection from electrostatic discharges
- Men's width
- Women's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

B0677 - Marathon S3 SRC **Commodity Code: 6404199000**

Test House

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)
Via Alberto Riva Villasanta, 3
, Italy
Cert No: F-113-03499-20

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
B0677BKB36	Black/Blue	67.0	41.0	36.0	1.0080	0.0989	8054633498729	
B0677BKB37	Black/Blue	67.0	41.0	36.0	1.0500	0.0989	8054633498736	
B0677BKB38	Black/Blue	67.0	41.0	36.0	1.0250	0.0989	8054633498743	
B0677BKB39	Black/Blue	67.0	41.0	36.0	1.1100	0.0989	8054633498750	
B0677BKB40	Black/Blue	67.0	41.0	36.0	1.1640	0.0989	8054633498767	
B0677BKB41	Black/Blue	67.0	41.0	36.0	1.1980	0.0989	8054633498774	
B0677BKB42	Black/Blue	67.0	41.0	36.0	1.1590	0.0989	8054633498781	
B0677BKB43	Black/Blue	67.0	41.0	36.0	1.2080	0.0989	8054633498798	
B0677BKB44	Black/Blue	67.0	41.0	36.0	1.2520	0.0989	8054633498804	
B0677BKB45	Black/Blue	67.0	41.0	36.0	1.3840	0.0989	8054633498811	
B0677BKB46	Black/Blue	67.0	41.0	36.0	1.4060	0.0989	8054633498828	
B0677BKB47	Black/Blue	67.0	41.0	36.0	1.3850	0.0989	8054633498835	
B0677BKB48	Black/Blue	67.0	41.0	36.0	1.4960	0.0989	8054633498842	