

161-62001

Article Number: 161-62001

Helawrap HWPP25 Convenience Pack, 1.0" Dia., Polypropylene, Black, 10.0ft/pkg



Base Data

Local Order Number	161-62001
Type	HWPP25
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none">• Unique open design for easy branch-offs at any point along the harness.• Overwrap formation provides abrasion protection and accommodates multiple bundle configurations.• Flexible construction and design eliminates pinch points and minimizes bending fatigue, making it ideal for applications involving movement and vibration.• Split shape allows for future access without disassembly.
Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.
Variant	Spiral Binding
Short Description	Helawrap HWPP25 Convenience Pack, 1.0" Dia., Polypropylene, Black, 10.0ft/pkg

Product Dimensions

Bundle Diameter min (imperial)	0.95 "
Bundle Diameter min (metric)	23 mm
Bundle Diameter max (imperial)	1.06 "
Bundle Diameter max (metric)	27 mm
Diameter D (imperial)	1.0 "
Diameter D (metric)	24.0 mm
Nominal Diameter (imperial)	1.0 "
Nominal Diameter (metric)	25.0 mm
Wall Thickness WT (imperial)	0.04 "
Wall Thickness WT (metric)	1.05 mm

Logistics and Packaging

Package Quantity (imperial)	10.0 ft
Package Quantity	10 ft
Carton Quantity	10.0 ft
Reel Length (metric)	3.05 m
Reel Length (imperial)	10.0 ft
Weight (imperial)	0.65 lbs

Material and Specifications

Material	Polypropylene (PP)
Material Shortcut	PP
Flammability	UL94 HB
Halogenfree	Yes
Operating Temperature	-22 °F to +194 °F (-30 °C to +90 °C)
ROHS Conformity	Yes