


Shock absorber DYSS-G8-5-5-Y1F

Part number: 8073914

FESTO



 General operating condition

Data sheet

Feature	Value
Size	5
Stroke	5 mm
Cushioning	Self-adjusting
Mounting position	optional
Position detection	Without
Symbol	00991495
Max. impact speed	1 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 80 °C
Cushioning length	5 mm
Max. stop force	200 N
Max. tightening torque	2 Nm
Max. energy consumption per stroke	1.4 J
Max. energy consumption per hour	8000 J
Max. residual energy	0.01 J
Reset force	0.9 N
Min. insertion force	10 N
Product weight	16 g
Load range	2.5 kg
Type of mounting	Via threaded sleeve
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	High-alloy steel
Material piston rod	High-alloy steel