



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKD XCKT XCMD XCKP
Associated head	ZCE01 ZCE05
Movement of operating head	Rotary
Type of operator	Pliable roller lever spring return metal (variable length)
Tracks	No track
Type of approach	Lateral approach

Complementary



Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available  Product environmental
Product end of life instructions	Need no specific recycling operations  End of life manual

Contractual warranty

Warranty period	18 months
-----------------	-----------