

Rotary Hammer LXT®

DHR264

18V X2 • SDS-PLUS • 26 mm • 2.5 J

Three-mode rotary hammer with quick-change chuck

An efficient rotary hammer with anti-vibration rear and side handles, for SDS-PLUS bits. Suited to impact and unstressed drilling and chipping. Speed range of 0 – 1 200 min⁻¹. Impact energy of 2.5 J and max. drilling capacity of 26 mm in concrete. .



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Impact Energy	2,5 J
Optimum Drilling Diameter Range in Concrete	4 - 18 mm
Max. Drilling Diameter in Concrete	26 mm
Max. Drilling Diameter in Wood	32 mm
Max. Drilling Diameter in Steel	13 mm
Impacts per Minute (IPM)	0 - 5000 min ⁻¹
No load speed	0 - 1250 min ⁻¹
Drilling diameter with TCT core bit	54 mm
Adapted for SDS-PLUS bits	✓
Tool weight with battery	3,5 - 4,7 kg
Vibration Level, Hammer Drilling Into Concrete	16,5 m/s ²

User benefits

- 36V performance from two 18V batteries connected in series. The batteries are placed in parallel in separate battery docking stations.
- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- One touch sliding chuck enables quick and easy bit changes
- Ergonomic chassis design ensures a good working position.
- Reversing switch
- LED light illuminates the work site
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing