



## Notice : 1567 350 DEM PH

Index : 2

### GUYARD SAS

22-24, rue Lucien Rouzet  
Z.A. Villedieu sur Indre/Niherne  
36250 NIHERNE FRANCE

### Intermediate Risks - PPE Category II

EN 420 :2003 +A1 :2009 EN 388 :2016  
EN 407 : 2004 EN ISO 13997 :1999  
EN 12477 :2001 +A1 :2005 Type A

#### Features:

- Glove: 5-finger cowhide split leather, American cut.
- Insulating Three-Piece Design: At the seams, junctions of the hand, thumb, and base of the cuff.
- Insulating Lining: Polyester.
- Stitching: Para-aramid thread.
- Length: 350 mm.

#### AVAILABLE SIZE: Size 10

#### Usage Precautions

- Wear the gloves on clean, dry hands. It is recommended to conduct a trial use of the gloves, as actual usage conditions may differ from EU type tests.
- Before each reuse, check that the gloves do not have defects, holes, tears, or abnormal wear.
- Expiry: 5 years from the manufacturing date indicated on the glove.

#### SAFETY, COMFORT, AND DEXTERITY:

##### Dexterity level 1

- The glove does not contain substances at levels known or suspected to have harmful effects on the hygiene or health of the user under foreseeable conditions of use.

#### PACKAGING

- In case of repackaging, a copy of the instruction manual must be included with the smallest packaging.
- Bag of 12 pairs
- Box of 60 pairs

#### MARKING :

- The CE marking on this glove indicates compliance with the essential health and safety requirements of the European Regulation 2016/425 regarding personal protective equipment (PPE).

#### RECOMMENDED USES:

- All applications requiring heat protection, such as welding work

EN 420 :2003+A1 :2009 EN 388 :2016 EN407 :2004



4 1 4 4 B

4 1 3 3 4 X

#### PERFORMANCE LEVELS :

##### EN 388 :2016

- Abrasion : 4/4
- Cut : 1/5
- Tear : 4/4
- Puncture : 4/4
- Cut (ISO 13997) : B/F

##### EN 407 :2004

- Fire Behavior : 4/4
- Contact heat : 1/4
- Convective heat : 3/4
- Radiant heat : 3/4
- Small metal splash: 4/4
- Large metal splash : X

##### EN 12477 :2001+ A1 /2005

- Type : A

#### PROTECTION Limits

- Do not use for handling objects with temperatures above 100°C.
- Do not use for handling chemicals or liquids..
- **Maintenance and Storage:**
- No special maintenance is recommended. It is advised to store the products in a cool, dry, and well-ventilated place , away from light.

#### End of life

- Disposal at end of life must be controlled and comply with European requirements for traceability and environmental protection.

EU Type Certificate issued in accordance with Module B of Regulation (EU) 2016/425

LEITAT ON n° :0162

The EU Declaration of Conformity is available at

[www.guyard-sa.com](http://www.guyard-sa.com)

Tél. +33 (0)2 54 35 63 70 • Télécopie +33 (0)2 54 35 63 70 • E-mail : [contacts@guyard-sa.com](mailto:contacts@guyard-sa.com)

Guyard S.A.S au capital de € 1 150 000,00 • SIRET 341 274 876 000034 • code APE 4642Z • TVA Intra : FR 19 341 274 876

